

Spider-80Hi Compared With Spider-80Xi

Application Note 092




Table of Figures

Table 1. Input Channel Specifications.....	2
Table 2. Output Channel Specifications.....	2
Figure 1. Noise floor with the Spider-80Xi V7.7 and the Spider-80Hi V8.9.....	3
Figure 2. THD with the Spider-80Xi V7.7 and the Spider-80Hi V8.9.....	3
Figure 3. CMMR at 1kHz with the Spider-80Xi V7.7 and the Spider-80Hi V8.9.....	3

Simran Parmar - Applications Engineer

April 2026 | © Crystal Instruments Corporation

The Spider-80Xi was first released in 2015. Crystal Instruments leveraged all the latest advances in electronics to develop the Spider-80Hi with major component upgrades, completed and released in 2025, delivering the following major upgrades:

- Sampling rate increased from 102.4 kHz (Spider-80Xi) to 512 kHz (Spider-80Hi)
- Spider-80Hi has ultra-low noise floor and significantly higher dynamic range of 175 dB
- Substantial performance improvements on both input and output channels
- Output DAC upgraded to 32-bit output at up to 768 kHz sampling rate, yielding very low output noise and high amplitude accuracy
- Amplitude linearity refined to 0.05 dB across the entire frequency range
- Additional signal integrity and noise improvements include:
- Isolation of digital and analog circuitry, combined with input channel front-end enhancements, minimizes ground loops for higher signal integrity
- Refinements in the IEPE constant current power supply significantly reduce noise at low frequencies

Together, these enhancements improve the system's precision and overall performance, making it well-suited for even the most demanding measurement applications.

Given the significant improvements across all performance specifications, Crystal Instruments chose to implement the best possible hardware — even though the upgrades make the new hardware incompatible with older counterparts. Existing customers and those looking to add channels are encouraged to upgrade to the v8.9 Spider-80Hi to take full advantage of

Specification	Spider-80Xi Version 7.7		Spider-80Hi Version 8.9	
Maximum Sampling Rate	102.4 kHz		512 kHz	
Noise (at 1 kHz)	80 nV/ $\sqrt{\text{Hz}}$		23.9 nV/ $\sqrt{\text{Hz}}$	
Dynamic Range	160 dBFs		175 dBFs	
Harmonic Distortion (2 V Input Signal)	Frequency	THD	Frequency	THD
	1 kHz	-94 dB	1 kHz	-105 dB
	8 kHz	-83 dB	8 kHz	-97 dB
Crosstalk	-100 dB		-120 dB	
Common Mode Rejection Ratio	-70 dB		-120 dB	
Amplitude Linearity	Amplitude Range (dBFS)	Amplitude Error	0.05 dB for entire amplitude range	
	0 to -80	0.1 dB		
	-20 to -100	0.25 dB		
	-120 to -120	0.5 dB		
	-120 to -140	1 dB		

Table 1. Input Channel Specifications

Specification	Spider-80Xi Version 7.7		Spider-80Hi Version 8.9	
Maximum Sampling Rate	102.4 kHz		512 kHz	
Output Resolution	24 bit		32 bit	
Dynamic Range	120 dB		127 dB	
Harmonic Distortion (1V output)	Frequency	THD	Frequency	THD
	1 kHz	-91 dB	1 kHz	-97 dB
	8 kHz	-78 dB	8 kHz	-94 dB
Crosstalk	120 dB		132 dB	

Table 2. Output Channel Specifications

the v8.9 hardware's performance and efficiency gains.

Spectrum plots regarding the improvements to noise floor and THD can be found in the next page. Full details regarding all specifications can be available upon request.

Comparison of Noise Floor:




Figure 1. Noise floor with the Spider-80Xi V7.7 and the Spider-80Hi V8.9. The 80Xi is in purple and 80Hi is in blue. dB reference is set to 20V (the full range of input)

Comparison of Total Harmonic Distortion:




Figure 2. THD with the Spider-80Xi V7.7 and the Spider-80Hi V8.9. The 80Xi is purple and the 80Hi is in blue.




Figure 3. CMMR at 1kHz with the Spider-80Xi V7.7 and the Spider-80Hi V8.9. The 80Xi is purple and the 80Hi is in blue.

ANALOG
DIGITAL



ADM Messtechnik GmbH & Co. KG · Zum Wartturm 9 · 63571 Gelnhausen
Tel. (06051) 916557-1 · sales@adm-messtechnik.de · www.adm-messtechnik.de

messtechnik

ADM Messtechnik GmbH & Co. KG

GERÄTE UND SYSTEME FÜR FORSCHUNG · ENTWICKLUNG · VERSUCH · SERVICE

Crystal Instruments Corporation
2090 Duane Avenue
Santa Clara, CA 95054

Crystal Instruments Testing Lab
15661 Producer Lane, STE H
Huntington Beach, CA 92649

Crystal Instruments Testing Lab
1548A Roger Dale Carter Boulevard
Kannapolis, NC 28081

Phone: +1 (408) 986-8880
Fax: +1 (408) 834-7818
www.crystallinstruments.com

© 2026 Crystal Instruments Corporation. All Rights Reserved. 04/2026

Notice: This document is for informational purposes only and does not set forth any warranty, expressed or implied, concerning any equipment, equipment feature, or service offered or to be offered by Crystal Instruments. Crystal Instruments reserves the right to make changes to this document at any time, without notice, and assumes no responsibility for its use. This informational document describes features that may not be currently available. Contact a Crystal Instruments sales representative for information on features and product availability.